

## **Transfer Cylinder Jacket** For Heidelberg® Presses



Print uard

MICROCELLULAR LAYER

US Patent 6,811,863

PrintGuardPlus Jackets for Heidelberg Presses

Microcellular Backed **AntiMarking Products** 

		9
	0	

PrintGuardPlus SM74T Jacket for Heidelberg SM-74 press

PrintGuard <i>Plus</i> Product Code (Stock Items)	Transfer Cylinde Jacket for Heidelberg Pres	
SM102RL	SM-102 Post 1993	
SM102LL	SM-102 Pre 1994	
SM74T	SM-74	
SM72T	SM-72	
MO26T	MOV	
SM52T	SM-52	
GT052T	GTO®-52	
THE PROPERTY OF		

Both Heidelberg and GTO are registered trademarks respectively, trademarks of Heidelberger Druckmaschinen AG in the U.S. and/or other countries.

PrintGuardPlus SM102RL Jacket for Heidelberg SM-102 press (post 1993)

Delivery and Perfecting Jackets also made to fit on Heidelberg Presses.

NEW Perfector Cylinder Jackets for Mitsubishi 3000D Press Custom Jackets Made Upon Request.

### **Care & Maintenance:**

For longest product life, clean PrintGuardplus Jackets with uniform light pressure using a cotton shop cloth saturated with water miscible mild press wash-preferably diluted 50/50 with water. Never let ink dry on the surface or use sharp tools or high abrasion to remove dried ink, let soak for a few minutes and wipe surface again with wet shop cloth.

PrintGuard, Orange Hide, and PrintGuardPlus are registered trademarks of PrintGuard, Inc. in the U.S. and/or other countries.

### **PrintGuard Guarantee**

The manufacturer and technical sales team stand behind PrintGuard's Performance! Buy two PrintGuardPlus jackets to confirm for yourself that PrintGuard will actually save you money by decreasing your press downtime and improving your print quality. Follow care and maintenance instructions below and if you are not satisfied with Printguard's performance, simply return these jackets within one month and we will refund the full product price.

# PRINTGUARD JACKETS

Perfect Fit for Your Heidelberg Press

